

Línea	Descripción del artículo	Order Code	Cantidad	Precio unitario CLP	Total (ML) CLP
1	***Promag 23P40, DN40 1 1/2"	23P40-ELOA1AA022AA	3	\$ 2,661.67	\$ 3,673.10
2	Cleanfit P CPA471	CPA471-A1A1A2B1	2	\$ 1,134.48	\$ 1,429.48
3	iTEMP TMT142, Field Transmitter HART	TMT142-A213AAAAA1	4	\$ 5,784.61	\$ 1,712.24
4	Liquisys M CLM223	CLM223-CD0005	1	\$ 517.37	\$ 320.77
5	Liquisys M CPM253	CPM253-PR0010	1	\$ 857.72	\$ 531.79
6	Minilog B RDL10	RDL10-R1B1A5	1	\$ 428.86	\$ 313.07
7	Promag 10H08, DN08 5/16"	10H08-1098/125	6	\$ 1,904.31	\$ 5,484.41
8	Promag 10H15, DN15 1/2"	10H15-10F9/125	6	\$ 1,904.31	\$ 5,484.41
9	Promag 10P80, DN80 3"	10P80-ELOA1AA0B4AA	3	\$ 2,325.07	\$ 3,208.59
10	Promag 10P80, DN80 3"	10P80-ELOA1AA0B4AA	1	\$ 2,325.07	\$ 1,069.53
11	Promag 10W50, DN50 2"	10W50-ULO1AG2B4AA	1	\$ 2,131.83	\$ 980.64
12	Promag 50, transmitter	50XXX-XXXXXAC0BAAW	1	\$ 1,601.99	\$ 736.91
13	Promag 50W25, DN25 1"	50W25-ULO1AC0BAAW	1	\$ 2,312.60	\$ 1,063.80
14	Promag 50W2F, DN250 10"	50W2F-UC0A1AA0BAAA	1	\$ 3,973.80	\$ 1,827.95
15	Promag 53, transmitter	53XXX-XXXXXAC4BAAA	1	\$ 2,125.60	\$ 977.77
16	Promag 53W1F, DN150 6"	53W1F-HR0B1AC4LAAK	3	\$ 4,243.71	\$ 5,856.32
17	Promag 53W8H, DN800 32"	53W8H-H91B1A54LAAK	1	\$ 13,323.93	\$ 6,129.01
18	Promag 55S2H, DN200 8"	55S2H-URJB1AS4BAAK	1	\$ 5,591.38	\$ 2,572.03
19	Promag W 800, 5W8B1H, DN100 4"	5W8B1H-1PX9/0	1	\$ 3,459.55	\$ 1,591.39
20	Promass 80F15, DN15 1/2"	80F15-1270/0	1	\$ 5,479.18	\$ 3,068.34
21	Promass 80F40, DN40 1 1/2"	80F40-2M60/0	1	\$ 6,657.29	\$ 3,728.08
22	Prowirl 72F15, DN15 1/2"	72F15-SK0BA1AAB4AW	4	\$ 2,069.50	\$ 3,725.09
23	Smartec S CLD132	CLD132-XAP150AB1	1	\$ 1,858.81	\$ 1,152.46