

Línea	Descripción del artículo	Order Code	Cantidad	Precio unitario CLP	Total (ML) CLP
1	***Promag 23P40, DN40 1 1/2"	23P40-ELOA1AA022AA	3	\$ 2,661.670	\$ 3,673.104
2	Cleanfit P CPA471	CPA471-A1A1A2B1	2	\$ 1,134.483	\$ 1,429.480
3	iTEMP TMT142, Field Transmitter HART	TMT142-A213AAAAA1	4	\$ 5,784.610	\$ 1,712.244
4	Liquisys M CLM223	CLM223-CD0005	1	\$ 517.374	\$ 320.772
5	Liquisys M CPM253	CPM253-PR0010	1	\$ 857.718	\$ 531.785
6	Minilog B RDL10	RDL10-R1B1A5	1	\$ 428.859	\$ 313.067
7	Promag 10H08, DN08 5/16"	10H08-1098/125	6	\$ 1,904.310	\$ 5,484.414
8	Promag 10H15, DN15 1/2"	10H15-10F9/125	6	\$ 1,904.310	\$ 5,484.414
9	Promag 10P80, DN80 3"	10P80-ELOA1AA0B4AA	3	\$ 2,325.065	\$ 3,208.590
10	Promag 10P80, DN80 3"	10P80-ELOA1AA0B4AA	1	\$ 2,325.065	\$ 1,069.530
11	Promag 10W50, DN50 2"	10W50-ULO1AG2B4AA	1	\$ 2,131.829	\$ 980.641
12	Promag 50, transmitter	50XXX-XXXXXAC0BAAW	1	\$ 1,601.988	\$ 736.914
13	Promag 50W25, DN25 1"	50W25-ULO1AC0BAAW	1	\$ 2,312.598	\$ 1,063.795
14	Promag 50W2F, DN250 10"	50W2F-UC0A1AA0BAAA	1	\$ 3,973.804	\$ 1,827.950
15	Promag 53, transmitter	53XXX-XXXXXAC4BAAA	1	\$ 2,125.596	\$ 977.774
16	Promag 53W1F, DN150 6"	53W1F-HR0B1AC4LAAK	3	\$ 4,243.712	\$ 5,856.324
17	Promag 53W8H, DN800 32"	53W8H-H91B1A54LAAK	1	\$ 13,323.930	\$ 6,129.008
18	Promag 55S2H, DN200 8"	55S2H-URJB1AS4BAAK	1	\$ 5,591.376	\$ 2,572.033
19	Promag W 800, 5W8B1H, DN100 4"	5W8B1H-1PX9/0	1	\$ 3,459.547	\$ 1,591.392
20	Promass 80F15, DN15 1/2"	80F15-1270/0	1	\$ 5,479.175	\$ 3,068.338
21	Promass 80F40, DN40 1 1/2"	80F40-2M60/0	1	\$ 6,657.292	\$ 3,728.084
22	Prowirl 72F15, DN15 1/2"	72F15-SK0BA1AAB4AW	4	\$ 2,069.496	\$ 3,725.092
23	Smartec S CLD132	CLD132-XAP150AB1	1	\$ 1,858.806	\$ 1,152.460